GEFRAN

1600P / 1800P

PROGRAMMER - CONTROLLER



Main features

- Universal input configurable from the faceplate
- Acquisition of the input signal every 120msec; resolution 30000steps
- Two control outputs: relay, logic or analogue with Heat/Cool function
- 3 configurable alarms
- 2 analogue outputs (setpoint retransmission)
- 2 digital inputs with configurable function
- Auxiliary input for C.T. or remote setpoint
- Heater Break or shortcircuit probe alarm
- Self and Auto-tuning, Soft-start, Local/Remote setpoint, Auto/Man
- 12 (16) steps arranged in max. 4 programs
- Second SP retransmitted to a slave controller, with same time-base

Main applications

- Plastics extrusion lines and injection moulding machines
- Polymerisation plant for synthetic fibre production
- Climatic chambers and test benches
- Continuous ovens and drying unit ceramics and bricks
- Chemical and pharmaceutical industries
- Furnaces
- · Food processing plant
- · Painting machines
- Water treatment
- Siderurgy industry
- · Packaging machinery

GENERAL

Microprocessor setpoint programmer and controller, format 48x96 / 96x96 (1/8 DIN - 1/4 DIN).

Manufactured using SMT, the instrument provides a complete operator interface, protected by a Lexan membrane that ensures level IP65 faceplate protection. It has 4 keys, two green LED displays, each with 4 digits, 4 red indicating LED's for the 4 logic or relay outputs, and a further 3 LED's that are programmable to indicate the various operational states of the instrument.

10 led red bargraph indication can be associated with analogue outputs for control, inputs or deviations.

The main input for the process variable is universal and provides the possibility to connect many types of input sensor: thermocouple, resistance thermometer, thermistor, linear inputs, potentiometer, all with the possibility of custom linearisation that can be defined using the faceplate keys. The type of input is selected from the faceplate keys and no external shunts or adapter are required.

A second auxiliary isolated analogue input is available, which can also be configured for a linear input, potentiometer or current transformer.

There are two isolated digital inputs for entering the program commands of start,

stop and reset, choosing the program and to step through the program.

The instrument can have up to 4 relay (5A/250V) or logic (11Vdc, 20mA) outputs and up to 2 isolated analogue outputs in voltage or current.

The function of each output is configurable and event outputs linked to the individual program step as well as control and alarm functions can be provided.

A further isolated output (10 or 24Vdc, 30mA max.) is available for powering external transmitters or potentiometers. The serial communication interface RS485 (RS232C compatible) makes it possible to read or modify any parameter and to govern the instrument online (local/remote manual/automatic commutation, internal timer control, direct control of outputs).

Protocols available: MODBUS RTU and CENCAL (Gefran).

The sequence for setting up the programmer is particularly brief and there are up to 8 steps, each with a setpoint ramp and hold.

It is also easy to set up any interlocks required from logic inputs and the event outputs, as well as the type of restart preferred using the few set-up steps in the "Step" menu.

The various steps can be regrouped in 4

different programs.

All the programming procedures of the instrument are facilitated by the grouping of the parameters in function blocks (**CFG** for the control parameters, **Inp** for the inputs, **Out** for the outputs, etc.) and by the possibility of selecting a simplified menu for entering the most frequently used parameters.

The instrument can also select the parameters is needs to display as a function of the hardware configuration, automatically concealing those that are not influential.

To simplify the configuration even further, a programming kit is available for PC, which includes a menu driven configuration program for Windows and the necessary cable to connect the instrument (see data sheet cod.WINSTRUM).

The programmer, as well as executing the program controlling the main output (heat/cool with two independent PID loops), can also retransmit 2 different setpoint profiles, with a common time base, to a slave controller using the two analogue outputs.

In the execution phase of the programmer, the two displays are used to monitor the behaviour of the program and make any necessary adjustments immediately.

TECHNICAL DATA

INPUTS

Accuracy 0,2% f.s. ±1digit. Acquisition of the input signal 120msec. Decimal point position for linear groups can be set freely.

For inputs from TC , RTD, PTC a decimal figure in the maximum display field (-199,9...999,9).

TC - Thermocouples

J (Fe-CuNi) 0...1000°C / 32...1832°F
K (NiCr-Ni) 0...1300°C / 32...2372°F
R (Pt13Rh-Pt) 0...1750°C / 32...3182°F
S (Pt10Rh-Pt) 0...1750°C / 32...3182°F
T (Cu-CuNi) -200...400°C / -328...752°F
B (Pt30Rh-Pt6Rh) 44...1800°C / 111...3272°F
E (NiCr-CuNi) -100...750°C / -148...1382°F
N (NiCrSi-NiSi) 0...1300°C / 32...2372°F
(Ni-Ni18Mo) 0...1100°C / 32...2012°F
L-GOST (NiCr-CuNi) 0...600°C / 32...1112°F
Custom

RTD 3-wires

Pt100 -200...850°C / -328...1562°F JPt100 (JIS C 1609/81)

-200...600°C / -328...1112°F

-1999...9999

Custom PTC

(alternative to RTD) -55...120°C / -67...248°F

Custom -1999...9999

DC - Linear

0...50mV; 10...50mV; 0...20mA 4...20mA; 0...10V; 2...10V Custom linearisation with 32 segment

Auxiliary input

insulation 1500V For remote setpoint: (0...10V, 2...10V, Ri=1M Ω) (0...20mA, 4...20mA, Ri=5 Ω) potentiometer > 500 Ω For current transformer:

CT 50mAac, 50/60Hz, Ri=1,5 Ω

Logic

Insulation 1500V NPN 24V/4,5mA (PNP 24V/3,6mA) Configurable function: Man/Auto, Loc/Rem, Alarms Reset,Hold, Setpoint selection.

OUTPUTS

Outputs fully configurable for: single alarm, "OR" or "AND" of multiple alarms, logic input repetition.

Relay

With rating: 5A/250V, $cos\phi=1$ (order code R)

Logic

11Vdc, Rout=220 Ω .=(20mA, max.6V) (order code D)

Analogue retransmission

isolated 1500V

- Up to 2 analogue outputs for control or retransmission (input signal, setpoint, auxiliary input, alarm setpoint).
- Scale range selectable from keyboard.
- Configurable output 0...10Vdc; 0...20/4...20mA
- Resolution 4000 steps

SERIAL LINE

Optoisolated 4-wires

Passive Current Loop configurable (1200 baud) interface, RS232 and RS422/485 (1200, 2400, 4800, 9600, 19200 baud). Protocol: GEFRAN CENCAL or MODBUS

POWER SUPPLY

Standard: 100 to 240Vac/dc ±10% on request: 20 to 27Vac/dc ±10% 50/60Hz; 12VAmax.

Protection by internal fuse not serviceable by the user

Transmitter Supply

isolated 1500V

10/24Vdc max. 30mA short circuit protection

AMBIENT CONDITION

Working temperature range: 0...50°C Storage temperature range: -20...70°C Humidity: 20...85%Ur non condensing

Control

Cooling setpoint relative to Heating setpoint

On/Off, P, PD, PID for heating and cooling with configurable parameters.

- Proportional band 0,0...999,9% f.s.
- Integral time 0,0...999,9 min
- Derivative time 0,0...99,99 min
- Max and min control output power limitation: 0,0...100,0%
- Manual Reset -999...999 digit
- Power Reset -100,0...100,0%
- Cycle time 0,1...200sec
- Soft-start 0,0...500,0 min

Alarms

- Up to 3 alarms, settable as absolute, deviation or symmetrical deviation alarm with respect to the control setpoint with configurable function (Hi or Lo).
- The alarm point may be set anywhere within the configured scale.
- Heater Break Alarm
- Loop Break Alarm
- Alarm Hysteresis configurable
- Alarms can be assigned to main input, auxiliary input or control SP.

WEIGHT

400g (1600P); 600g (1800P) in complete version

FACEPLATE DESCRIPTION

A - PV Display: process variable

B - SV Display: setpoint value

C - "Function" key


D - "Lower" key

E - "Raise" key

F - "Automatic/Manual" selection


G - Function indication

H - Indication of active outputs




Double green LED display (4 Digit) Faceplate protection IP65


DIMENSIONS AND CUT OUT



CONNECTION DIAGRAM



ORDER CODE



GEFRAN spa reserves the right to make any kind of design or functional modification at any moment without prior notice.



Conformity C/UL/US File no. E216851



The instrument conforms to the European Directives 2004/108/CE and 2006/95/CE with reference to the generic standards: - EN 61000-6-2 (immunity in industrial environment) - EN 61000-6-3 (emission in residential environment) - EN 61010-1 (safety)



C - TICK

